



מבוא לכניסה לאתר



כניסה ל-Endress+Hauser Portal Instrumentrics Industrial Control LTD



ברוך הבא
Please login to the Endress+Hauser
!Portal

e00800312 * זיהוי משתמש
●●●●●●●●●● * סיסמה

כניסה למערכת

בעיות בכניסה למערכת? קבלת תמיכה

Maintenance Information

Due to maintenance work the services on <https://portal.endress.com> are not available on Sunday, November 11 from 6 a.m. to 1 p.m. CET

We apologize for any inconvenience.

מתוך התפריטים השונים בחר: "Installed Base Assistant" (ניתן לעיין בתפריטיים הנוספים)

The screenshot shows the Endress+Hauser W@M Portal website. At the top, there is a navigation bar with the text "People for Process Automation" on the left and the Endress+Hauser logo on the right. Below the navigation bar, there is a header section with the text "Welcome, Guest User" and a navigation menu with links for "Home", "Engineering", "Procurement", and "Installation, Commissioning, Operations". The main content area is divided into several sections:

- Endress+Hauser W@M Portal**: A section describing the W@M Life Cycle Management concept, which is a set of tools and solutions to help improve processes during the phases of the life cycle - engineering, procurement, installation and operations. At each phase, W@M will help save you time and money by helping to manage your instrumentation.
- Engineering & Procurement**: A section with six icons and links for various tools and services, including:
 - Find the right device according to your process parameters ([Applicator Selection module](#))
 - Size devices according to your process parameters ([Applicator Sizing module](#))
 - Find most suitable devices for your applications and industry ([Applicator Industry Applications module](#))
 - Get prices and order online ([Online Shop](#))
 - Check the delivery status of your orders ([Shipment tracking](#))
 - Manage your project information ([Project Engineering Assistant](#))
- Manage your installed base**: A section with six icons and links for various tools and services, including:
 - Access to your installed base ([Installed base assistant](#))
 - Manage working tasks ([Task scheduler](#))
 - Find spare parts references ([Spare part finding tool](#))
 - Check device availability ([Product status list](#))
 - Download documentation ([Download area](#))
- W@M Life Cycle Management latest News**: A section with a heading "Welcome to W@M Portal 4.0" and a paragraph of text. Below the text, there are three icons and links for "Setup email notification" ([Automatic status notification](#)), "Help", and "Contact us".
- Preferences**: A section with a heading "Preferences" and a link for "Setup email notification" ([Automatic status notification](#)).


At the bottom right of the page, there is a zoom level indicator showing "125%".

"Installed Base" 3 לפניך

Instrumentrics demo center-ב בחר

(ניתן גם לעיין בהמשך באופציה אחרת כדוגמת "Chocolate Company Freiburg")

People for Process Automation

Endress+Hauser 

Welcome, Guest User W@M Help | Profile | Sign out

Home | Engineering | Procurement | **Installation, Commissioning, Operations**

Installed Base Assistant | Product Status | Find Spares for Product | Download Area | Status Report

Installation, Commissioning, Operations > Installed Base Assistant

Search

Search


Device

Search

Installed Base Assistant

Version 07.01.02s

Manage your installed Base



Installed Base selection

Name ↕	Permission ↕
Chocolate Company Freiburg	Read only
Instrumentrics demo center	Read only
Instrumentrics Industrial	Read only

of 3

125%

מה ניתן לבחור מתוך "View" ?

People for Process Automation

Welcome, Guest User

Endress+Hauser **EH**

Home | Engineering | Procurement | **Installation, Commissioning, Operations**

W@M Help | Profile | Sign out

Installed Base Assistant | Product Status | Find Spares for Product | Download Area | Status Report

Installation, Commissioning, Operations > Installed Base Assistant

Navigation | Query

View Location tree

instrumetrics demo center
e00800296, Feb 5, 2013

Open tasks

Instrumetrics demo center
ישראל

Key performance indicators | Product Status check | Device list (35) | Attachments (0)

Overview

Devices	35	critical	1
Loops	0	critical	0
Applications	0	critical	0
Buses	4		
Locations	0		

Base matrix

	Σ	0	0	1	1
Process criticality ↑		0	0	1	1
		0	0	0	0
		0	0	0	0
		0	0	0	0
					Σ

Risk of maintainability →

Current product status (only for Endress+Hauser instruments)

Order stop	1
Phase out	0
Available	12

125%

רשימת ייצרני מכשור וציוד

People for Process Automation

Welcome, Guest User

Home Engineering Procurement **Installation, Commissioning, Operations**

Installed Base Assistant Product Status Find Spares for Product Download Area Status Report

Installation, Commissioning, Operations > Installed Base Assistant

Navigation Query

View Manufacturer tree

- Instrumentics demo center
 - ABB
 - Acromag
 - Endress+Hauser
 - Pepperl + Fuchs
 - Procentec
 - Samson

Installed Base Instrumentics demo center
Last update e00800296, Feb 5, 2013

Open tasks

Instrumentics demo center
ישראל

Key performance indicators Product Status check Device list (35) Attachments (0)

Overview

Devices	35	critical	1
Loops	0	critical	0
Applications	0	critical	0
Buses	4		
Locations	0		

Base matrix

	Σ	0	0	1	1
Process criticality ↑		0	0	1	1
		0	0	0	0
		0	0	0	0
		Σ	0	0	0
		Risk of maintainability →			

Current product status (only for Endress+Hauser instruments)

Order stop	1
Phase out	0
Available	12

סוגי מכשור וציוד

Process Automation

Welcome, Guest User

Home Engineering Procurement **Installation, Commissioning, Operations**

Installed Base Assistant Product Status Find Spares for Product Download Area Status Report

Installation, Commissioning, Operations > Installed Base Assistant

Navigation Query

View Device type tree

✂️ 📄 🗑️ 📁

📁 **instrumetrics_demo_center**

- ⊕ ⚠️ 2 Channel Repeater
- ⊕ ⚠️ Communication, Hardware and :
- ⊕ ⚠️ Electro-Magnetic Flow Measure
- ⊕ ⚠️ Electro-Mechanical Systems
- ⊕ ⚠️ Gateway
- ⊕ ⚠️ Liquline
- ⊕ ⚠️ Microwave Level Measurement
- ⊕ ⚠️ Others
- ⊕ ⚠️ pH/ORP Measurement
- ⊕ ⚠️ PLC
- ⊕ ⚠️ Process Pressure
- ⊕ ⚠️ Remote I/O
- ⊕ ⚠️ Scope PA Coupler
- ⊕ ⚠️ Scope Repeater
- ⊕ ⚠️ Start Motor
- ⊕ ⚠️ Transmitter
- ⊕ ⚠️ Ultrasonic Level Measurement
- ⊕ ⚠️ Unknown

Installed Base Instrumetrics demo center
Last update e00800296, Feb 5, 2013

Open tasks ○○○ 📄 🗑️ 📁

Instrumetrics demo center
ישראל

Key performance indicators Product Status check Device list (35) Attachments (0)

Overview

Devices	35	critical	1
Loops	0	critical	0
Applications	0	critical	0
Buses	4		
Locations	0		

Base matrix

	Σ	0	0	1	1
Process criticality		0	0	1	1
		0	0	0	0
		0	0	0	0
					Σ

Risk of maintainability

Current product status (only for Endress+Hauser instruments)

	Order stop	1
	Phase out	0
	Available	12

רשתות תקשורת

Process Automation

Welcome, Guest User

Home | Engineering | Procurement | **Installation, Commissioning, Operations**

Installed Base Assistant | Product Status | Find Spares for Product | Download Area | Status Report

Installation, Commissioning, Operations > Installed Base Assistant

Navigation | Query

View: Bus tree

- [-] Instrumetrics demo center
 - [+] CO104_PB
 - [+] CO105_FF
 - [+] CO106_FF
 - [+] Hart_FXA520

Installed Base Instrumetrics demo center

Last update e00800296, Feb 5, 2013

Open tasks ○○○

Instrumetrics demo center

ישראל

Key performance indicators | **Product Status check** | Device list (35) | Attachments (0)

Overview

Devices	35	critical	1
Loops	0	critical	0
Applications	0	critical	0
Buses	4		
Locations	0		

Base matrix

Σ	0	0	1	1
Process criticality ↑	0	0	1	1
	0	0	0	0
	0	0	0	0
	→ Risk of maintainability			Σ

Current product status (only for Endress+Hauser instruments)

	Order stop	1
	Phase out	0
	Available	12

רשימת הזמנות מכשור

People for Process Automation

Welcome, Guest User

Home Engineering Procurement **Installation, Commissioning, Operations**

Installed Base Assistant Product Status Find Spares for Product Download Area Status Report

Installation, Commissioning, Operations > Installed Base Assistant

Navigation Query

View Customer-order-

Instrumetrics demo center

- + 01/51007389/11023526
- + 01/51038330/11215455
- + 12-7465
- + 3-12028
- + 30035215-Israel
- + 45012044/30
- + Austauschgerät

Device list (1)

TAG	Order code	Manufacturer	Serial number	Label 1
AIT001	CPM253-PR0305	Endress+Hauser	62013C05G00	

of 1

נתחיל לעיין בסביבת: רשתות תקשורת

(נבחר ברשת Profibus DP : CO104_PB)

Process Automation

Welcome, Guest User

Home | Engineering | Procurement | **Installation, Commissioning, Operations**

Installed Base Assistant | Product Status | Find Spares for Product | Download Area | Status Report

Installation, Commissioning, Operations > Installed Base Assistant

Navigation | Query

View: Bus tree

- ✂
- 📄
- 🗑
- 📁
- 🔍
- 🔧
- 📄

- [-] Instrumetrics demo center
 - + CO104_PB
 - + CO105_FF
 - + CO106_FF
 - + Hart_FXA520

Installed Base Instrumetrics demo center
Last update e00800296, Feb 5, 2013
Open tasks ○○○

Instrumetrics demo center
 ישראל

Key performance indicators | Product Status check | Device list (35) | Attachments (0)


Overview

Devices	35	critical	1
Loops	0	critical	0
Applications	0	critical	0
Buses	4		
Locations	0		

Base matrix


Σ	0	0	1	1
Process criticality ↑	0	0	1	1
	0	0	0	0
	0	0	0	0
	→ Risk of maintainability			Σ

Current product status (only for Endress+Hauser instruments)

	Order stop	1
	Phase out	0
	Available	12

בתוך תפריט זה ניתן למצוא תרשימים של הרשת

People for Process Automation

Endress+Hauser 

Welcome, Guest User W@M Help | Profile | Sign out

Home | Engineering | Procurement | **Installation, Commissioning, Operations**

Installed Base Assistant | Product Status | Find Spares for Product | Download Area | Status Report

Installation, Commissioning Operations > Installed Base Assistant



Navigation Query

View Bus tree

Instrumetrics demo center

- CO104_PB
 - 961PB-2006
 - 966PB-2006
 - 972PB-2006
 - 983PB-2012
 - AIT001
 - AIT002
 - CO104
 - Comb Scope DP PA Coupler
 - Comb Scope Repeater NW 1
 - Comb Scope Repeater Spar
 - COMbricks-Head-Station-1C
 - CPBPW_SC
 - FIT001
 - FXA_720_DP_04
 - M1
 - M2
 - M3
 - PB_ASI_GATE
 - TCV001
 - TT001
 - TT002
- CO105_FF
- CO106_FF
- Hart_FXA520

Name CO104_PB

Open tasks  

Instrumetrics demo center
ישראל

Device list (21) Bus details Attachments (5)

Name	L1	Type	Version
Other			
ba034sen.pdf	XX		
Guideline__Assembling_8022_v106_May06.pdf	XX		
Default			
CO104_PB NetTestII Online Report.TXT	XX		
CO104_PB Network	XX		
Operating instruction			
EM Betriebsanleitung CM442 / CM444 / CM448	DE	Doc.	2011.12.15

6 of 8

Name CO104_PB Network | Version

Category | Language


Add file CO104.jpg

Do you want to open or save CO104.jpg from portal.endress.com? Open Save Cancel

125%

תרשים של הרשת

Profibus DP/PA CO104 Network



Designed by Tzvi Ben Yosef



רשימת המכשור והציוד בהתאם ל-TAG לדוגמת RI/O של חב' Acromag

Process Automation

Welcome, Guest User

Home | Engineering | Procurement | **Installation, Commissioning, Operations**

Installed Base Assistant | Product Status | Find Spares for Product | Download Area | Status Report

Installation, Commissioning, Operations > **Installed Base Assistant**

Navigation | Query

View: Bus tree

- Instrumetrics demo center
 - CO104_PB
 - 961PB-2006**
 - 966PB-2006
 - 972PB-2006
 - 983PB-2012
 - AIT001
 - AIT002
 - CO104
 - Comb Scope DP PA Coupler
 - Comb Scope Repeater NW 1
 - Comb Scope Repeater Span
 - COMbricks-Head-Station-1C
 - CPBPW_SC
 - FIT001
 - FXA_720_DP_04
 - M1
 - M2
 - M3
 - PB_ASI_GATE
 - TCV001
 - TT001
 - TT002
 - CO105_FF
 - CO106_FF
 - Hart FXA520

TAG	961PB-2006
Order code	
Device type	Remote I/O
Manufacturer	Acromag
Open tasks	<input type="radio"/> <input type="radio"/> <input type="radio"/> <input type="radio"/>

Instrumetrics demo center
ישראל

Overview | Detail | Attachments (2) | Spare parts | Logbook | More product information

TAG	961PB-2006
Serial number	225093E
Order code	
Order number	
Short name	
Template	Instrument
Device type	Remote I/O
Manufacturer	Acromag
Date of manufacture	
Software version	
Equipment remarks	


Environment conditions Not defined

Criticality Not defined

Risk of maintainability Not defined

Device location information

Product Status No information available



ניתן לגשת למסמכים מצורפים, לעיין בהם ולהוריד אותם למחשב

People for Process Automation

Welcome, Guest User

Home | Engineering | Procurement | **Installation, Commissioning, Operations**

Installed Base Assistant | Product Status | Find Spares for Product | Download Area | Status Report

Installation, Commissioning, Operations > Installed Base Assistant

Navigation | Query

View: Bus tree

- Instrumetrics demo center
 - CO104_PB
 - 961PB-2006**
 - 966PB-2006
 - 972PB-2006
 - 983PB-2012
 - AIT001
 - AIT002
 - CO104
 - Comb Scope DP PA Coupler
 - Comb Scope Repeater NW 1
 - Comb Scope Repeater Span
 - COMbricks-Head-Station-1C
 - CPBPW_SC
 - FIT001
 - FXA_720_DP_04
 - M1
 - M2
 - M3
 - PB_ASI_GATE
 - TCV001
 - TT001
 - TT002
 - CO105_FF
 - CO106_FF
 - Hart_FXA520

TAG: 961PB-2006

Order code: 961PB-2006

Device type: Remote I/O

Manufacturer: Acromag

Open tasks: [Progress indicator]

Instrumetrics demo center
ישראל

Name	L1	Type	Version
Product picture			
961PB-2006.jpg		XX	
Operating instruction			
961_962EN_720e.pdf		XX	

4 of 4

Name: 961_962EN_720e.pdf | Version: []

Category: Operating instruction | Language: []

Add to: []

Add file: [] | 961_962EN_720e.pdf

Do you want to open or save 961_962EN_720e.pdf from portal.endress.com?

Open Save Cancel

125%

בחירת מכשיר המחובר ב- Profibus PA לדוגמת TT002

Process Automation

Welcome, Guest User

Home Engineering Procurement **Installation, Commissioning, Operations**

Installed Base Assistant Product Status Find Spares for Product Download Area Status Report

Installation, Commissioning, Operations > Installed Base Assistant

Navigation Query

View Bus tree

Instrumentics demo cent

- CO104_PB
 - 961PB-2006
 - 966PB-2006
 - 972PB-2006
 - 983PB-2012
 - AIT001
 - AIT002
 - CO104
 - Comb Scope DP
 - Comb Scope Rep
 - Comb Scope Rep
 - COMbricks-Head
 - CPBPW_SC
 - FIT001
 - FXA_720_DP_04
 - M1
 - M2
 - M3
 - PB_ASI_GATE
 - TCV001
 - TT001
 - TT002**
- CO105_FF
- CO106_FF
- Hart_FXA520

TAG TT002
Order code TMT84-A1A2A
Device type Transmitter
Manufacturer Endress+Hauser

Open tasks


Instrumentics demo center
 ישראל

Overview Detail Attachments (19) Spare parts Logbook More product information

TAG TT002
Serial number E3019C142B6
Order code TMT84-A1A2A
Order number
Short name iTEMP TMT84, Transmitter PA
Template Instrument
Device type Transmitter
Manufacturer Endress+Hauser
Date of manufacture 2011
Software version
Equipment remarks

Environment conditions Not defined
Criticality Not defined
Risk of maintainability Low

Device location information
 Product Status Available



ניתן לבחור מסמך לעיון שנוצר ע"י FieldCare

People for Process Automation

Welcome, Guest User

Home | Engineering | Procurement | **Installation, Commissioning, Operations** | W@M Help | Profile | Sign out

Installed Base Assistant | Product Status | Find Spares for Product | Download Area | Status Report

Installation, Commissioning, Operations > Installed Base Assistant

Navigation | Query

View: Bus tree

Instrumetrics demo center

- CO104_PB
 - 961PB-2006
 - 966PB-2006
 - 972PB-2006
 - 983PB-2012
 - AIT001
 - AIT002
 - CO104
 - Comb Scope DP
 - Comb Scope Ref
 - Comb Scope Ref
 - COMbricks-Head
 - CPBPW_SC
 - FIT001
 - FXA_720_DP_04
 - M1
 - M2
 - M3
 - PB_ASI_GATE
 - TCV001
 - TT001
 - TT002**
 - CO105_FF
 - CO106_FF
 - Hart_FXA520

TAG TT002
Order code TMT84-A1A2A
Device type Transmitter
Manufacturer Endress+Hauser
Open tasks

Instrumetrics demo center
ישראל

Overview | Detail | **Attachments (19)** | Spare parts | Logbook | More product information

Name	L1	L2	L3	Type	Version
ATEX Safety instructions TEMP@ TMT84 and TMT85	EN	DE	FR	Doc.	2008.01.01
ATEX Safety instructions TEMP@ TMT84 and TMT85	EN	DE	FR	Doc.	2008.01.01
Default					
FieldCareConfiguration_121029_TT002.xml		XX			
FieldCareConfiguration_121029_TT002.pdf		XX			
FieldCareConfiguration_121111_TT002.xml		XX			
FieldCareConfiguration_121030_TT002.pdf		XX			
FieldCareConfiguration_121029_TT002.xml		XX			
FieldCareConfiguration_121030_TT002.xml		XX			
FieldCareConfiguration_121029_TT002.pdf		XX			

9 of 26

Name: FieldCareConfiguration_12102 | Version:

Category: | Language:

Add to:

Add file: CF_E3019C142B6_20121029-

Do you want to open or save CF_E3019C142B6_20121029-130939.pdf from portal.endress.com?

Open Save Cancel

125%

חלק מהדו"ח

Adobe Reader window showing a PDF document titled "CF_E3019C14286_20121029-130939.pdf". The document content is as follows:

Diagnostics

Parameter	Value
Current diagnostics	482C
Current diagnostics description	Simulation mode active
Status channel	1
Status count	1
Diagnostics	More information available. function check
Last diagnostics	482C
Last status channel	1
Clear last diagnostics	Show last error
Enabled features	Condensed status and diagnostics enabled
Supported features	Condensed Status and Diagnostics information Status and Diagnostics as 3.01described in profile
Setting condensed status diagnostics	Condensed Status and Diagnostics information is provided
Service locking	0


System information

Parameter	Value
-----------	-------

The screenshot also shows the Windows taskbar at the bottom with various application icons and the system tray displaying the date 10/02/2013 and time 09:42.

ניתן לבחור מסמך לעיון שנוצר ע"י FieldCare המשווה הבדלים במצב המכשיר בין שני תאריכים שונים

People for Process Automation

Endress+Hauser 

Welcome, Guest User

Home | Engineering | Procurement | **Installation, Commissioning, Operations** | W@M Help | Profile | Sign out

Installed Base Assistant | Product Status | Find Spares for Product | Download Area | Status Report

Installation, Commissioning, Operations > Installed Base Assistant

Navigation | Query

View Bus tree

- Instrumentics demo cent
 - CO104_PB
 - 961PB-2006
 - 966PB-2006
 - 972PB-2006
 - 983PB-2012
 - AIT001
 - AIT002
 - CO104
 - Comb Scope DP
 - Comb Scope Ref
 - Comb Scope Ref
 - COMbricks-Head
 - CPBPW_SC
 - FIT001
 - FXA_720_DP_04
 - M1
 - M2
 - M3
 - PB_ASI_GATE
 - TCV001
 - TT001
 - TT002**
 - CO105_FF
 - CO106_FF
 - Hart_FXA520

TAG: TT002
 Order code: TMT84-A1A2A
 Device type: Transmitter
 Manufacturer: Endress+Hauser

Instrumentics demo center
 ישראל

Open tasks

Overview | Detail | **Attachments (19)** | Spare parts | Logbook | More product information

Name	L1	L2	L3	Type	Version
FieldCareConfiguration_121111_TT002.pdf	XX				
Certificate					
Control Drawing CSA Intrinsic Safety, Non incendive ITEMP® TMT84 andITEMP® TMT85	EN			Doc.	2007.12.02
Control Drawing FM Intrinsic Safety, Non incendive ITEMP® TMT84 andITEMP® TMT85	EN			Doc.	2007.12.02
Technical information					
Technical Information ITEMP® TMT84	EN			Doc.	2008.08.01
Service document					
TT002 Historical Online Comparison	XX				
Operating instruction					
Brief operating instructionsITEMP® TMT84	EN	DE	FR	Doc.	2008.07.01

22 of 26

Name: TT002 Historical Online Compa | Version:

Category: Service document | Language:

Add to:

Add file: TT002 Historical online compar

Do you want to open or save TT002 Historical online comparison.pdf from portal.endress.com?


Open | Save | Cancel

125%

מסמך השוואה שנוצר ע"י FieldCare אשר משווה פרמטרים של מכשיר בין 2 תאריכים

Parameter compare

Tag: TT002

Endress+Hauser  People for Process Automation

online - - 13:09 29/10/12 online 22:13 05/02/13

	Identification	Identification
dtmName	ITEMP / TMT84 / PA / V1.0	ITEMP / TMT84 / PA / V1.0
dtmVersion	1.5.140.318	1.5.140.318
	TMT84	TMT84
Diagnostics		
Current diagnostics	C482	G000
Current diagnostics description	Simulation mode active	Good
Status channel	1	0
Status count	1	0
Measured values		
PV value 1	26.189 °C	25.656 °C
Process temperature 1	26.189 °C	25.656 °C
RJ temperature 1	30.649 °C	29.076 °C
RJ temperature 2	30.655 °C	29.076 °C
Expert		
Communication		
Analog Input 1		
Static Revision No.	97	167
Output Value	50.000 Not used	25.651 Not used
Fail Safe Mode	Storing last valid Output Value.	The calculated output value is incor
All simulation quality	Good	J.
All simulation status	OK	J.
All simulation value	50.000	J.
All simulation enable	Enabled	Disabled
Diagnostics		
Current diagnostics	C482	G000
Current diagnostics description	Simulation mode active	Good
Status channel	1	0
Status count	1	0
Diagnostics	More information available, function check	
Last diagnostics	C482	C402
Last status channel	1	0
Measured values		
PV value 1	26.189 °C	25.651 °C
Process temperature 1	26.189 °C	25.651 °C
RJ temperature 1	30.665 °C	29.076 °C
Sensor raw value 1	110.194	109.987
RJ temperature 2	30.665 °C	29.081 °C
Quality	J.	Good
Status	J.	OK
Quality	J.	Good
Status	J.	OK
Quality	J.	Good
Status	J.	OK
Quality	J.	Good
Status	J.	OK

- כל מה שקדם מהווה פתיח להמשך הסיור שלכם באתר זה.

תהנו!!